

PXI/DAQ/DAQe-2208

96-CH 12-Bit 3 MS/s Ultra High-Density Analog Input Cards



Introduction

ADLINK's PXI/DAQ/DAQe-2208 are ultrahigh-density and high-performance analog input cards. These devices can sample up to 96 AI channels with different gain settings and scan sequences, making them ideal for dealing with ultrahigh-density analog signals with various input ranges and sampling speeds. These devices also offer differential mode for 48 AI channels in order to achieve maximum noise elimination.

The PXI/DAQ/DAQe-2208 also features analog and digital triggering and 24-CH programmable digital I/O lines. Like all the other members in the PXI/DAQ/DAQe-2000 family, the PXI/DAQ/DAQe-2208 are able to perform analog input at full speed while multiple cards can be synchronized through the SSI (System Synchronization Interface) bus. The auto-calibration functions adjust the gain and offset to within specified accuracies so that you do not have to adjust trim pots to calibrate the cards.

Features

- Supports a 32-bit 3.3 V or 5 V PCI bus (DAQ-2208)
- x1 lane PCI Express® Interface (DAQe-2208)
- PXI Specification Rev. 2.2 compliant (PXI-2208)
- 96-CH single-ended or 48-CH differential analog inputs
- Onboard 1 k-sample A/D FIFO
- Bipolar or unipolar analog input ranges
- Programmable gains of x1, x2, x4, x5, x8, x10, x20, x40, x50, x200
- 1024-configuration channel gain queue
- Scatter-gather DMA for analog inputs
- 24-CH TTL digital input/output
- Analog and digital triggering
- Fully auto calibration
- Multiple cards synchronization through SSI (System Synchronization Interface) bus or PXI trigger bus
- Operating Systems
 - Windows 7/Vista/XP/2000/2003 Server
 - Linux
- Recommended Software
 - AD-Logger
 - VB.NET/VC.NET/VB/VC+++/BCB/Delphi
 - DAQBench
- Driver Support
 - DAQPilot for LabVIEW™
 - DAQ-MTLB for MATLAB®
 - D2K-DASK for Windows
 - D2K-DASK/X for Linux

Terminal Boards & Cables

DIN-68S-01

Terminal Board with One 68-pin SCSI-II Connector and DIN-Rail Mounting (Cables are not included.)

ACL-10568-1

68-pin SCSI-VHDCI cable (mating with AMP-787082-7), 1 M

* For more information on mating cables, please refer to P2-61/62.

Pin Assignment

Connector CN1 Pin Assignment

AI0 (AIH0)	1	35	(AIL0) AI48
AI1 (AIH1)	2	36	(AIL1) AI49
AI2 (AIH2)	3	37	(AIL2) AI50
AI3 (AIH3)	4	38	(AIL3) AI51
AI4 (AIH4)	5	39	(AIL4) AI52
AI5 (AIH5)	6	40	(AIL5) AI53
AI6 (AIH6)	7	41	(AIL6) AI54
AI7 (AIH7)	8	42	(AIL7) AI55
AISENSE	9	43	AI GND
AI8 (AIH8)	10	44	(AIL8) AI56
AI9 (AIH9)	11	45	(AIL9) AI57
AI10 (AIH10)	12	46	(AIL10) AI58
AI11 (AIH11)	13	47	(AIL11) AI59
AI12 (AIH12)	14	48	(AIL12) AI60
AI13 (AIH13)	15	49	(AIL13) AI61
AI14 (AIH14)	16	50	(AIL14) AI62
AI15 (AIH15)	17	51	(AIL15) AI63
AI16 (AIH16)	18	52	(AIL16) AI64
AI17 (AIH17)	19	53	(AIL17) AI65
AI18 (AIH18)	20	54	(AIL18) AI66
AI19 (AIH19)	21	55	(AIL19) AI67
AI20 (AIH20)	22	56	(AIL20) AI68
AI21 (AIH21)	23	57	(AIL21) AI69
AI22 (AIH22)	24	58	(AIL22) AI70
AI23 (AIH23)	25	59	(AIL23) AI71
AI GND	26	60	AI GND
AI24 (AIH24)	27	61	(AIL24) AI72
AI25 (AIH25)	28	62	(AIL25) AI73
AI26 (AIH26)	29	63	(AIL26) AI74
AI27 (AIH27)	30	64	(AIL27) AI75
AI28 (AIH28)	31	65	(AIL28) AI76
AI29 (AIH29)	32	66	(AIL29) AI77
AI30 (AIH30)	33	67	(AIL30) AI78
AI31 (AIH31)	34	68	(AIL31) AI79

Pin Assignment

Connector CN2 Pin Assignment


AI32 (AIH32)	1	35	(AIL32) AI80
AI33 (AIH33)	2	36	(AIL33) AI81
AI34 (AIH34)	3	37	(AIL34) AI82
AI35 (AIH35)	4	38	(AIL35) AI83
AI36 (AIH36)	5	39	(AIL36) AI84
AI37 (AIH37)	6	40	(AIL37) AI85
AI38 (AIH38)	7	41	(AIL38) AI86
AI39 (AIH39)	8	42	(AIL39) AI87
EXTATRIG	9	43	AI GND
AI40 (AIH40)	10	44	(AIL40) AI88
AI41 (AIH41)	11	45	(AIL41) AI89
AI42 (AIH42)	12	46	(AIL42) AI90
AI43 (AIH43)	13	47	(AIL43) AI91
AI44 (AIH44)	14	48	(AIL44) AI92
AI45 (AIH45)	15	49	(AIL45) AI93
AI46 (AIH46)	16	50	(AIL46) AI94
AI47 (AIH47)	17	51	(AIL47) AI95
AI GND	18	52	AI GND
N/C	19	53	N/C
EXTDTRIG	20	54	AFI0
EXTTIMEBASE	21	55	DGND
PB7	22	56	PB6
PB5	23	57	PB4
PB3	24	58	PB2
PB1	25	59	PB0
PC7	26	60	PC6
PC5	27	61	PC4
DGND	28	62	DGND
PC3	29	63	PC2
PC1	30	64	PC0
PA7	31	65	PA6
PA5	32	66	PA4
PA3	33	67	PA2
PA1	34	68	PA0

SSI Bus Cables

(for multiple cards synchronization)

ACL-SSI-2/3/4

SSI Bus cable for two, three, and four devices



Ordering Information / Quick Selection Guide

Model Name	Analog Input				Analog Output			DIO	Timer/Counter
	No. of channels	Resolution	Sampling rate	Input range	No. of channels	Resolution	Update rate	No. of channels	No. of channels
PXI/DAQ/DAQe-2208	48 DI/96 SE	12 bits	3 MS/s	±0.05 V to ±10 V	-	-	-	24-bit 8255 PIO	-

Specifications

Model Name	PXI/DAQ/DAQe-2208
Analog Input	
Resolution	12 bits, no missing codes
Number of channels	96 single-ended or 48 differential
Channel gain queue size	1024
Maximum sampling rate	3 MS/s
Programmable gain	1, 2, 4, 5, 8, 10, 20, 40, 50, 200
Bipolar input ranges	±10 V, ±5 V, ±2.5 V, ±2 V, ±1.25 V, ±1 V, ±0.5 V, ±0.25 V, ±0.2 V, ±0.05 V
Unipolar input ranges	0-10 V, 0-5 V, 0-4 V, 0-2.5 V, 0-1 V, 0-0.5 V, 0-0.4 V, 0-0.1 V
Offset error	±2 mV
Gain error	±0.06% of FSR
Input Coupling	DC
Overvoltage protection	Power on: Continuous ±30 V, Power off: Continuous ±15 V
Input Impedance	1 GΩ/100 pF
CMRR (gain = 1)	90 dB
Settling time	1 μs to 0.1 % error *
-3 dB small signal bandwidth (gain = 1)	2 MHz
Trigger sources	Software, external digital/analog trigger, SSI bus
Trigger modes	Pre-trigger, post-trigger, middle-trigger, delay-trigger, and repeated trigger
FIFO buffer size	1 k samples
Data Transfers	Polling, scatter-gather DMA
Digital I/O	
Number of channels	24-CH 8255 programmable input/output
Compatibility	5 V/TTL
Data transfers	Programmed I/O
Auto Calibration	
Onboard reference	+5 V
Temperature drift	±2 ppm/°C
Stability	±6 ppm/1000 Hrs
General Specifications	
Dimensions	160 mm x 100 mm (not including connectors) (PXI-2208) 175 mm x 107 mm (not including connectors) (DAQ-2208) 168 mm x 107 mm (not including connectors) (DAQe-2208)
Connector	68-pin VHDCI female x 2
Operating temperature	0 to 55°C
Storage temperature	-20 to 70°C
Humidity	5 to 95%, non-condensing
Power requirements	+5 V 0.95 A typical (PXI/DAQ-2208) +3.3 V 0.81 A, +12 V 0.568 A typical (DAQe-2208)

*Gain = 1, 2, 4, 8